



Alfa Laval Service Manuals

April, 2015

Sanitary Products

- Pumps
- Valves
- Miscellaneous
- Control Tops and Positioners





Alfa Laval Service Manuals

April, 2015

Pumps

- LKH-110, -120 Multi-Stage Centrifugal Pump
 - LKH Centrifugal Pump
 - LKH Ultrapure Centrifugal Pump
 - LKH Evap Centrifugal Pump
 - LKHP Filtration Centrifugal Pump for High Inlet Pressure
 - MR-166S, -185S, -200S Liquid-Ring Pump
 - MR-300 Liquid-Ring Pump
 - SolidC Pump
 - SRU Rotary Lobe Pump
 - SRU Rotary Lobe Pump ATEX Addendum
 - SX Rotary Lobe Pump
 - SX Rotary Lobe Pump ATEX Addendum
-
- Tri-Blender Series





Alfa Laval Service Manuals

April, 2015

Valves

- 650-655-660 Manual and Air-Actuated Fractional Valves
- 700 Series Air-Actuated Valves
- 762-862 Flow Diversion Valves and Panel (Models 762-227, 762-227/MRAL & 862W-227)
- ARC with Reduced Stroke Aseptic Remote-Controlled Valve
- ARC Aseptic Remote-Controlled Valve with PTFE Diaphragm
- CPM-2 Constant Pressure Modulating Valve
- CPM-I-D60 constant-Pressure Modulating Inlet Valve
- Keofitt Aseptic Membrane Sampling Valve
- Koltek Valve
- LKB Automatic or Manual Butterfly Valve and LKB-LP Low Pressure Butterfly Valve
- LKB UltraPure Automatic or Manual Butterfly Valve
- SBV Sanitary Ball Valve
- SMO (Sanitary Manual Valve)
- SPC-1 (SRC Style) Sanitary Proportional-Controlled Valve with Positioner
- Unique SPC-1 Regulating Valve
- SPC-2 Sanitary Electro-Pneumatic Modulating Valve
- SRC Sanitary Remote-Controlled Valve
- 5308 5309 Ball Valve/Ball Valve Tri-Clover
- 5308 5309 Ball Valve/Ball Valve UltraPure
- Unique 7000 6 Inch Valve
- Unique 7000 Aseptic Valve
- Unique 7000 Long Stroke Valve
- Unique 7000 Manually Operated Valve
- Unique 7000 Standard and Reverse-Acting Valve
- Unique 7000 Tangential Body/Tank Valve
- Unique 7000 Series Tank Outlet Valve
- Unique 7000 Series Valve - Two Step
- Unique 7000 Y Body Valve
- Unique 7000 7710 Regulating Valve
- Unique Mixproof Tank Outlet Valve
- Unique Sanitary Mixproof Valve (including US Versions)
- Unique Small Single Seat Valve
- Unique PMO Cheese Curd Sanitary Mixproof Valve
- Unique PMO Sanitary Mixproof Valve
- Unique PMO Plus Mixproof Valve
- Unique PMO Plus CP Mixproof Valve
- Unique PMO Plus CP Horizontal Tank Valve
- Unique PMO Plus CP Vertical Tank Valve
- Unique Sanitary Mixproof LP and LP-F
- Unique RV-ST Regulating Valve
- Unique Sampling Valve - Type P - Pneumatic Operated
- Unique Sampling Valve - Type M - Manually Operated
- Unique DV-ST Ultrapure - Manual
- Unique DV-ST Ultrapure - Pneumatic
- Radial Diaphragm Valve UltraPure





Alfa Laval Service Manuals

April, 2015

Control Tops and Positioners

- ThinkTop AS Interface 31 nodes & 62 nodes
- ThinkTop Basic AS Interface 62 nodes
- ThinkTop Basic Digital 10 - 30 VDC PNP/NPN
- ThinkTop Basic Intrinsically Safe
- ThinkTop Devicenet™ 11 - 25 VDC
- ThinkTop Digital 8 - 30 or 110 VAC NO/NC
- Thinktop Digital 8 - 30 VDC PNP/NPN
- ThinkTop Quick Setup Guide
- ThinkTop for 700 Series Valves AS-Interface 29.5-31.5
- ThinkTop for 700 Series Valves Digital 8 - 30 VDC PNP NPN
- RV-ST 8692 Positioner Instruction Manual
- RV-ST 8692 Positioner Quick Start
- RV-ST 8694 Positioner Instruction Manual
- RV-ST 8694 Positioner Quick Start
- ThinkTop D30
- GreenTop for Single Seat Valves
- IndiTop Mounting Instructions
- ThinkTop Indication Pin





Alfa Laval Service Manuals

April, 2015

Miscellaneous

- [LLC Liquid Level Control](#)
- [Mainstream and Streamline Filters-Strainers](#)
- [PD340 Magnetic Flow Transmitter PD 210 Display Unit](#)
- [GHVB Vacuum Breaker](#)
- [Unique Vacuum Breaker](#)

